

# Product data sheet

## Characteristics

# EZMR114225

Branch unit, EZ Meter-Pak, 225A, 4 sockets, 120/240VAC, no bypass, ringless, 800A Al busbar



### Main

|                         |                          |
|-------------------------|--------------------------|
| Product                 | Meter Center Branch Unit |
| Current Rating          | 225 A                    |
| Type                    | Meter-Pak                |
| Bus Rating              | 800 A                    |
| Number of Jaws          | 5 without jaw release    |
| Number of Meter Sockets | 4                        |
| Bypass Type             | No bypass                |
| Socket Type             | Ringless                 |

### Complementary

|                        |                           |
|------------------------|---------------------------|
| Certifications         | UL Listed                 |
| Busbar Material        | Aluminium busbar          |
| Enclosure Material     | Steel                     |
| Enclosure Rating       | NEMA 3R                   |
| Maximum Voltage Rating | 120/240 V AC              |
| Mounting               | Surface                   |
| Phase                  | 1 phase in<br>1 phase out |
| Wire Configuration     | 3-wire                    |
| Height                 | 52.00 in (1320.80 mm)     |
| Width                  | 17.38 in (441.45 mm)      |
| Depth                  | 8.09 in (205.49 mm)       |

### Ordering and shipping details

|                       |                      |
|-----------------------|----------------------|
| Category              | 00020 - EZ METER-PAK |
| Discount Schedule     | DE4                  |
| GTIN                  | 00785901333036       |
| Nbr. of units in pkg. | 1                    |
| Package weight(Lbs)   | 88 lb(US) (39.92 kg) |
| Returnability         | Yes                  |
| Country of origin     | MX                   |

### Packing Units

|                  |                   |
|------------------|-------------------|
| Package 1 Height | 0.78 ft (0.239 m) |
| Package 1 width  | 1.65 ft (0.503 m) |
| Package 1 Length | 4.42 ft (1.346 m) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|