

Product data sheet

Characteristics

2510MCW1

Manual Starter, integral horsepower, NEMA M1, 600 VAC, 2 pole, 3 HP at 230 VAC, single phase, no indicator, NEMA 4/4X



Main

Product	Manual Starter
Type	M
NEMA Size	M-1

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	2 Hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase
Voltage Rating	600 V AC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	12.13 in (308.10 mm)
Width	6.5 in (165.10 mm)
Depth	6.41 in (162.81 mm)

Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
NEMA Enclosure Rating	NEMA 4/4X glass polyester

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901455943
Nbr. of units in pkg.	1
Package weight(Lbs)	19.66 lb(US) (8.92 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------