

Product data sheet

Characteristics

9080LBC363101

Power distribution block, Linergy, 3 pole, 1 line, 1 load, 255A CU, 600 V



Main

Range	9080LB
Product	Power Distribution Block
Current Rating	255 A copper

Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number of poles	3
Terminals per Pole	1 line 1 load
Wire Size	Line 1, AWG 6...250 kcmil, copper Load 1, AWG 6...250 kcmil, copper
Electrical Connection	Tin plated copper lugs
SCCR	100 kA UL 508 A
Ambient air temperature for operation	-40...302 °F (-40...150 °C)
Block Material	Phenolic block
Terminal Tightening Torque	Line lug 375 lbf.in (42.37 N.m) AWG 6...250 kcmil copper or aluminium Load lug 375 lbf.in (42.37 N.m) AWG 6...250 kcmil copper or aluminium
Wire stripping length	Line 1.19 in (30.23 mm) Load 1.19 in (30.23 mm)
Height	4 in (101.60 mm)
Width	5 in (127.00 mm)
Depth	2.61 in (66.29 mm)
End Barrier	9080LB33

Environment

Certifications	CE CSA file 70361 class 6228 01 UL recognized E60616 CCN XCFR2
----------------	--

Ordering and shipping details

Category	21711 - 9080 LB
Discount Schedule	CP1
GTIN	00785901097679
Nbr. of units in pkg.	1
Package weight(Lbs)	1.86 lb(US) (0.84 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.00 in (7.62 cm)
Package 1 width	4.40 in (11.176 cm)
Package 1 Length	5.40 in (13.716 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	16
Package 2 Weight	30.85 lb(US) (13.993 kg)
Package 2 Height	11.30 in (28.702 cm)
Package 2 width	9.50 in (24.13 cm)
Package 2 Length	13.40 in (34.036 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------