



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz
Hold-in power consumption in VA	35 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	10P 10 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901485988
Nbr. of units in pkg.	1
Package weight(Lbs)	10.83 lb(US) (4.91 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	7.30 in (18.542 cm)
Package 1 width	8.20 in (20.828 cm)
Package 1 Length	13.00 in (33.020 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

