



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120 V AC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Combination ARC-fault
Electrical Connection	Pressure plate
Connections Terminals	Pigtail neutral

Complementary

Interrupt Rating	10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium AWG 14...AWG 10 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.75 in (120.65 mm)
Width	0.75 in (19.05 mm)
Depth	2.91 in (73.91 mm)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	06303-QO ARC FAULT CB
Discount Schedule	DE2A
GTIN	00785901007012
Package weight(Lbs)	4.00 oz (113.398 g)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration