



Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P
[I _{th}] conventional free air thermal current	25 A
I ² t on activation	200000 A ² .s
Number of cables	3 0.01 in ² (4 mm ²) 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	7.48 in (190 mm)
Depth	2.40 in (61 mm)

Complementary

[Ui] rated insulation voltage	690 V IEC 60439-1
9 mm pitches	6
Net Weight	0.51 lb(US) (0.23 kg)

Environment

Standards	IEC 60439
Product certifications	UL DNV CSA LROS (Lloyds register of shipping)

Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	00785901576723
Nbr. of units in pkg.	1
Package weight(Lbs)	0.82 lb(US) (0.37 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.36 in (6 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	8.66 in (22 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Weight	17.79 lb(US) (8.068 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	160
Package 3 Weight	163.94 lb(US) (74.364 kg)

Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------