



Main

| | |
|--------------|--------------------------------|
| Product Type | Industrial Control Transformer |
| Power Rating | 300 VA |
| Type | T |

Complementary

| | |
|--------------------------------|---|
| Number of Phases | 1 phase |
| Power Rating | 300 VA UL 300 VA CSA 300 VA NOM 200 VA |
| Temperature Rise | 80 °C |
| Electrical Connection | Screw clamp terminals |
| Height | 3.84 in (97.54 mm) |
| Width | 4.5 in (114.30 mm) |
| Depth | 4.74 in (120.40 mm) |
| Material | Copper winding |
| Fingersafe Cover Compatibility | FSC2 |

Environment

| | |
|------------------------|--|
| Certifications | UL listed file E61239 CSA file LR37055 guide 184-N-90 |
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 266 °F (130 °C) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 16206 - 9070 T (NOT TF) MTO |
| Discount Schedule | CP8 |
| GTIN | 00785901313908 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 6.40 in (16.256 cm) |
| Package 1 width | 6.80 in (17.272 cm) |
| Package 1 Length | 7.70 in (19.558 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |

Contractual warranty

| | |
|----------|----------|
| Warranty | 10 Years |
|----------|----------|