

# JDL36250C

Circuit breaker, PowerPacT J, unit mount, thermal-magnetic, 250A, 3 pole 14 kA, 600 VAC, 100% rated



## Main

Product or component type	Circuit breaker
---------------------------	-----------------

## Complementary

Number of Poles	3P
Breaking capacity code	D
Magnetic hold current	1250 A
Magnetic tripping current	2500 A
Electrical connection	Lugs load Lugs line
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in <sup>2</sup> (95...185 mm <sup>2</sup> ) (AWG 3/0...350 kcmil)
Height	7.52 in (191.01 mm)
Width	4.12 in (104.65 mm)
Depth	5 in (127.00 mm)
Continuous current rating	100 %

## Ordering and shipping details

Category	01110-HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901923336
Package weight(Lbs)	4.50 lb(US) (2.041 kg)
Returnability	Yes
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---

Approximate Dimensions

