



Main

Product or component type	All-In-One
Range of product	Homeline
Meter socket type	Ringless
Hub type	A

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Mounting	Surface
Number of spaces	20
Number of circuits	40
Number of Tandem Breakers	20
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil aluminium)line side AWG 6...350 kcmil copper)line side AWG 12...AWG 2/0 aluminium)service ground AWG 12...AWG 2/0 copper)service ground
Tightening torque	Main lugs 250 lb.in, AWG 6...350 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14...AWG 2/0, copper Service ground 50 lb.in, AWG 12...AWG 2/0, aluminium Branch lugs 50 lb.in, AWG 14...AWG 1/0, copper Branch lugs 50 lb.in, AWG 12...AWG 1/0, aluminium Branch lugs 35 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Width	14.37 in (365.00 mm)
Depth	5.07 in (128.78 mm)
Height	36.69 in (931.93 mm)

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Disconnect Schedule	DE3A
GTIN	00785901193364
Nbr. of units in pkg.	1
Package weight(Lbs)	42.37 lb(US) (19.22 kg)

Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.80 in (14.732 cm)
Package 1 width	14.90 in (37.846 cm)
Package 1 Length	36.40 in (92.456 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	21
Package 2 Weight	928.00 lb(US) (420.933 kg)
Package 2 Height	45.60 in (115.824 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------