



Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	12

Complementary

Number of ways	3 ways N + 3 L
Poles configuration for 1 way	1 x 3P + N 1 x 4P
Connection pitch	0.71 in (18 mm)
Connector type	Tooth
Distance between way	2.83 in (72 mm)
Marking	N L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	100 A 104 °F (40 °C)
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top or bottom tunnel type terminals Top or bottom double terminal
9 mm pitches	24
Width	8.66 in (220 mm)
Color	White (RAL 9003)
Range compatibility	Acti 9 iC60 Acti 9 iK60 Acti 9 iID Acti 9 iID K Acti 9 iSW Acti 9 iSW-NA Multi 9 C60

Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	1760 °F (960 °C) 30 s) IEC 60695-2-1
Pollution degree	3 IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	03606480485060
Nbr. of units in pkg.	5
Package weight(Lbs)	0.52 lb(US) (0.24 kg)
Returnability	No
Country of origin	DE

Packing Units

Package 1 Height	0.300 dm
Package 1 width	0.200 dm
Package 1 Length	2.140 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------