



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	41.57 in (1056 mm)
Nominal width	33.54 in (852 mm)
Nominal depth	13.78 in (350 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 1 lock
Door type	Solid
Lock type	4 points lock, handle with 5 mm double bar insert

Complementary

Number of locks	1
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	NEMA classification 13 IEC 62208 NEMA classification 4X
Product certifications	UL
Electrical insulation class	Class II

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for operation	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901047926
Nbr. of units in pkg.	1
Package weight(Lbs)	68.2 lb(US) (30.93 kg)
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	41.57 in (105.6 cm)
Package 1 width	13.78 in (35 cm)
Package 1 Length	33.54 in (85.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile