



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	20 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	VDE UL
Material	Body extruded aluminium Cover plastic
Height	External 3.86 in (98 mm)
Width	External 1.50 in (38 mm)
Depth	External 2.95 in (75 mm)
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By clips
Mounting support	35 mm DIN rail

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901179481
Nbr. of units in pkg.	1
Package weight(Lbs)	0.48 lb(US) (0.22 kg)
Returnability	No
Country of origin	ES

Packing Units

Package 1 Height	1.77 in (45.000 mm)
Package 1 width	4.33 in (110.000 mm)
Package 1 Length	3.15 in (80.000 mm)

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------