

# Product data sheet

## Characteristics

# 9999TC10

Disconnect mechanism, flange mounted, disconnect switch auxiliary contact kit, 15A, 1 pole, SPDT



### Main

Range	Square D
Product or component type	Interlock
Device application	Control

### Complementary

Range compatibility	Disconnect Switch
[Ie] rated operational current	15 A120 V AC 50/60 Hz 15 A240 V AC 50/60 Hz 15 A480 V AC 50/60 Hz 15 A600 V AC 50/60 Hz
Height	4.16 in (105.66 mm)
Depth	1.44 in (36.58 mm)
Net Weight	0.51 lb(US) (0.23 kg)

### Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901858478
Nbr. of units in pkg.	1
Package weight(Lbs)	0.51 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	3.20 in (8.128 cm)
Package 1 width	4.20 in (10.668 cm)
Package 1 Length	6.70 in (17.018 cm)

### Offer Sustainability

EU RoHS Directive	Under investigation
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.