

Product data sheet

Characteristics

NSYAMPM2924TB

Mounting plate in galvanized steel, thickness 1.5 mm For boxes of H275W225 mm



Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Back studs
Mounting plate description	Plain
Range compatibility	Thalassa TBS Thalassa TBP
Device composition	1 mounting plate
Material	Galvanised steel

Complementary

Fixing mode	By screws M4 self tapping - on back studs
Height	Nominal 11.46 in (291 mm) Real 8.46 in (215 mm)
Width	Nominal 9.49 in (241 mm) Real 10.43 in (265 mm)
Thickness	0.06 in (1.5 mm)
Net Weight	0.57 lb(US) (0.26 kg)

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901809241
Nbr. of units in pkg.	1
Package weight(Lbs)	1.01 lb(US) (0.46 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.08 in (0.2 cm)
Package 1 width	8.46 in (21.5 cm)
Package 1 Length	10.43 in (26.5 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
