

Product data sheet

Characteristics

EZML113225

Branch unit, EZ Meter-Pak, 225A, 3 sockets,
120/240 VAC, lever bypass, ringless, 1200A Al/
Cu busbar



Main

Product	Meter Center Branch Unit
Current Rating	225 A
Type	Meter-Pak
Bus Rating	1200 A
Number of Jaws	5 with jaw release
Number of Meter Sockets	3
Bypass Type	Lever bypass
Socket Type	Ringless

Complementary

Certifications	UL Listed
Busbar Material	Aluminium/copper busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	120/240 V AC
Mounting	Surface
Phase	1 phase in 1 phase out
Wire Configuration	3-wire
Height	53.06 in (1347.72 mm)
Width	19.44 in (493.78 mm)
Depth	9.44 in (239.78 mm)

Ordering and shipping details

Category	00020 - EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901408826
Nbr. of units in pkg.	1
Package weight(Lbs)	142 lb(US) (64.41 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.98 in (27.9 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	54.02 in (137.2 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Weight	944.00 lb(US) (428.191 kg)
Package 2 Height	38.00 in (96.52 cm)
Package 2 width	42.00 in (106.68 cm)
Package 2 Length	60.00 in (152.4 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------