



Main

| | |
|---------------------------|-------------------------------|
| Product or component type | Shunt trip |
| Circuit breaker type | H-frame J-frame L-Frame |

Complementary

| | |
|-------------------|--|
| Rated voltage | 380...480 V AC |
| Tightening torque | 12.39 lbf.in (1.4 N.m) 0.00...0.00 in ² (0.82...2.5 mm ²) (AWG 18...AWG 14) |

Environment

| | |
|------------------------|-----|
| Product certifications | CSA |
|------------------------|-----|

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES |
| Discount Schedule | DE2 |
| GTIN | 00785901589914 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.28 lb(US) (0.13 kg) |
| Returnability | Yes |
| Country of origin | US |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.