



### Main

Range	TeSys
Device short name	LA4SK
Product or component type	Suppressor module
Product compatibility	LC1SK06 LP1SK06 CA2SK LC1SKGC CA3SK
Suppressor technology	Varistor (peak limiting)
Quantity per set	Set of 10

### Complementary

Mounting location	Right hand side
[Uc] control circuit voltage	110...250 V AC 110...250 V DC
Maximum peak voltage	2 Uc
Net Weight	0.01 lb(US) (0.003 kg)

### Environment

Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Ambient air temperature for storage	-58...158 °F (-50...70 °C)

### Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
GTIN	00785901866794
Nbr. of units in pkg.	1
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	Yes
Country of origin	CZ

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	4.72 in (12 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.27 oz (36 g)
Package 2 Height	1.57 in (4 cm)
Package 2 width	1.97 in (5 cm)
Package 2 Length	4.72 in (12 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	190
Package 3 Weight	30.69 oz (870 g)

Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------