



Main

Range of product	Lineryg
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.00 in ² (0.5 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	White
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG gauge	AWG 22
Bezel size	Ø 3.1 mm
Tube diameter	0.05 in (1.3 mm)
Length	0.55 in (14 mm)
Tube length	0.31 in (8 mm)
Net Weight	0.20 lb(US) (0.09 kg)

Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901537120
Nbr. of units in pkg.	1000
Package weight(Lbs)	1000 lb(US) (453.59 kg)
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.20 in (0.5 cm)
Package 1 width	0.20 in (0.5 cm)
Package 1 Length	0.59 in (1.5 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	100
Package 2 Weight	0.30 oz (8.4 g)

Package 2 Height	0.39 in (1 cm)
Package 2 width	0.79 in (2 cm)
Package 2 Length	2.56 in (6.5 cm)
Unit Type of Package 3	BB1
Number of Units in Package 3	1000
Package 3 Weight	3.17 oz (90 g)
Package 3 Height	0.98 in (2.5 cm)
Package 3 width	4.33 in (11 cm)
Package 3 Length	6.69 in (17 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------