

### Main

Product or component type	Braking resistor
---------------------------	------------------

### Complementary

Range compatibility	Altivar Process ATV900 Altivar Machine ATV340
Product compatibility	Variable speed drive ATV930 wall mount 5.5 kW 380...480 V medium cycle Variable speed drive ATV930 wall mount 7.5 kW 380...480 V medium cycle Variable speed drive ATV950 wall mount 5.5 kW 380...480 V medium cycle Variable speed drive ATV950 wall mount 7.5 kW 380...480 V medium cycle Variable speed drive ATV930 wall mount 1.5 kW 200...240 V severe cycle Variable speed drive ATV340 4 kW 380...480 V medium cycle Variable speed drive ATV340 5.5 kW 380...480 V medium cycle Variable speed drive ATV930 7.5 kW 500...690 V medium cycle Variable speed drive ATV930 11 kW 500...690 V medium cycle Variable speed drive ATV930 10 hp 600 V medium cycle Variable speed drive ATV930 15 hp 600 V medium cycle
Braking cycle	Severe cycle heavy duty) <4 s 100 % 120 s Medium cycle normal duty) <4 s 135 % 40 s Medium cycle heavy duty) <4 s 165 % 40 s Severe cycle heavy duty) <6 s 165 % 120 s
Average power available	0.5 kW 122 °F (50 °C)
Ohmic value	60 Ohm
Electrical connection	Terminal <= 10 mm <sup>2</sup> / AWG 8 drive
Protection type	Thermal protection via drive
Width	6.89 in (175 mm)
Height	18.31 in (465 mm)
Depth	3.94 in (100 mm)
Net Weight	8.38 lb(US) (3.8 kg)

### Environment

Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	-13...158 °F (-25...70 °C)
IP degree of protection	IP20

### Ordering and shipping details

Category	22209 - ATV650
Discount Schedule	CP4E
GTIN	03606480802348
Nbr. of units in pkg.	1
Package weight(Lbs)	9.6 lb(US) (4.35 kg)
Returnability	No
Country of origin	DE

## Packing Units


Unit Type of Package 1	PCE
Package 1 Height	7.09 in (18 cm)
Package 1 width	7.28 in (18.5 cm)
Package 1 Length	18.90 in (48 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Weight	134.09 lb(US) (60.82 kg)
Package 2 Height	31.50 in (80 cm)
Package 2 width	31.50 in (80 cm)
Package 2 Length	23.62 in (60 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

Dimensions

Right Side and Front View



Dimensions in mm

A	B	C	A1	C1	Ø
175	100	465	142	436	4.5

Dimensions in in.


A	B	C	A1	C1	Ø
6.89	3.94	18.31	5.59	17.16	0.18

Mounting and Clearance



(1) Braking resistor

mm  
in.




---

Recommended Schema


---

1 Braking Resistor



- A1 : Drive or external braking unit
- A2 : Braking resistor
- PA, Bus DC
- PB :
- T1, Temperature control switch
- T2 :

2 Braking Resistors



- A1 : Drive or external braking unit
- A2 : Braking resistor
- PA, Bus DC
- PB :
- T1, Temperature control switch
- T2 :