

# Product data sheet

## Characteristics

# MP86200

MP Meter Pak, main lugs, six ringed sockets, no bypass, 4 jaws, OH, UG, 800 A bus, 200 A, 240 VAC single phase 3W



### Main

Product	Meter Center
Socket Rating	200 A
Main Type	Main Lugs
Number of Jaws	4
Number of Meter Sockets	6
Socket Type	Ringed

### Complementary

Main Rating	600 A 750 A
Bus Rating	800 A
Certifications	UL Listed
Type	Meter-Pak
Busbar Material	Aluminium busbar
Bypass Type	No bypass
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	240 V AC
Mounting	Surface
Phase	1 phase
Service Feed Location	OH UG
Wire Size	AWG 3/0...500 kcmil 2 aluminium AWG 3/0...500 kcmil 2 copper
Wire Configuration	3-wire
Height	43.41 in (1102.61 mm)
Width	46.68 in (1185.67 mm)
Depth	8.28 in (210.31 mm)

### Ordering and shipping details

Category	00021 - METER-PAK
Discount Schedule	DE4
GTIN	00785901410447
Nbr. of units in pkg.	1
Package weight(Lbs)	167 lb(US) (75.75 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	0.82 ft (0.249 m)
Package 1 width	3.75 ft (1.143 m)
Package 1 Length	3.92 ft (1.194 m)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------