



Main

Circuit Breaker Type	PJL PLL MJL PKL PGL MGL
Product Destination	Circuit breaker M 2P Circuit breaker P 3P

Complementary

Enclosure Material	Stainless Steel
Width	20.75 in (527.05 mm)
Height	40.83 in (1036.96 mm)
Depth	9.50 in (241.3 mm)
Rated Current	300...800 A
Poles Description	2P 3P
Product Weight	89.00 lb(US) (40.37 kg)

Environment

Product Certifications	UL CSA
------------------------	-----------

Environmental

NEMA Degree of Protection	NEMA 3 NEMA 5 NEMA 4 NEMA 4X NEMA 3R
NEMA Degree of Protection	NEMA 3 NEMA 5 NEMA 4 NEMA 4X NEMA 3R

Ordering and shipping details

Category	00031 - IND CB ENC N 4,4X,5,12,12K
Discount Schedule	DE1
GTIN	00785901669890
Nbr. of units in pkg.	1
Package weight(Lbs)	86.86 lb(US) (39.40 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.07 ft (0.325 m)
Package 1 width	1.88 ft (0.572 m)
Package 1 Length	3.63 ft (1.107 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------