

# Product data sheet

## Characteristics

# NSYAMPM1916TB

Mounting plate in galvanized steel, thickness 1.5 mm For boxes of H175W150 mm



### Main

|                                    |                              |
|------------------------------------|------------------------------|
| Range                              | Thalassa                     |
| Accessory / separate part category | Mounting accessory           |
| Product or component type          | Mounting plate               |
| Device application                 | Multi-purpose                |
| Enclosure nominal dimensions       | -                            |
| Mounting location                  | Back studs                   |
| Mounting plate description         | Plain                        |
| Range compatibility                | Thalassa TBS<br>Thalassa TBP |
| Device composition                 | 1 mounting plate             |
| Material                           | Galvanised steel             |

### Complementary

|             |                                                     |
|-------------|-----------------------------------------------------|
| Fixing mode | By screws M4 self tapping - on back studs           |
| Height      | Nominal 7.56 in (192 mm)<br>Real 5.51 in (140 mm)   |
| Width       | Nominal 6.46 in (164 mm)<br>Real 66.34 in (1685 mm) |
| Thickness   | 0.06 in (1.5 mm)                                    |
| Net Weight  | 0.22 lb(US) (0.1 kg)                                |

### Ordering and shipping details

|                       |                                       |
|-----------------------|---------------------------------------|
| Category              | 80036 - ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule     | ES1                                   |
| GTIN                  | 00785901947202                        |
| Nbr. of units in pkg. | 1                                     |
| Package weight(Lbs)   | 2.2 lb(US) (1.00 kg)                  |
| Returnability         | No                                    |
| Country of origin     | FR                                    |

### Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 0.08 in (2.000 mm)   |
| Package 1 width  | 5.51 in (140.000 mm) |
| Package 1 Length | 6.69 in (170.000 mm) |

### Offer Sustainability

|                        |                                                                                                |
|------------------------|------------------------------------------------------------------------------------------------|
| REACH Regulation       | <a href="#">REACH Declaration</a>                                                              |
| REACH free of SVHC     | Yes                                                                                            |
| EU RoHS Directive      | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free | Yes                                                                                            |
| Mercury free           | Yes                                                                                            |

---

|                            |                                        |
|----------------------------|----------------------------------------|
| RoHS exemption information | <a href="#">Yes</a>                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |

---

### Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---