

# Product data sheet

## Characteristics

# UGHTRS213C

Individual meter socket, ringless socket, horn bypass, 5 jaws no release, OH, UG, 200 A, up to 600 VAC single phase 3W



### Main

Product or component type	Meter Socket
Meter socket type	Ringless
Hub type	A ACP closing plate

### Complementary

Meter socket rated current	200 A
Number of jaws	5 without jaw release
Bypass type	Horn bypass
Phase	1 phase
[Ue] rated operational voltage	<= 600 V AC
Enclosure material	Steel
Electrical connection	Lugs 0.5" hex
Service feed location	UG OH
Wiring configuration	3-wire
Device mounting	Surface
AWG gauge	AWG 8...350 kcmil aluminium/copper)line side

### Environment

Product certifications	ANSI UL Listed
Enclosure Rating	NEMA 3R

### Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901282679
Nbr. of units in pkg.	1
Package weight(Lbs)	13.06 lb(US) (5.92 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	5.60 in (14.224 cm)
Package 1 width	11.60 in (29.464 cm)
Package 1 Length	15.70 in (39.878 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation

## Contractual warranty

Warranty	18 months
----------	-----------