



### Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Rear panel
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Rear of enclosure
Quantity per set	Set of 1

### Complementary

Range compatibility	Spacial SF
Device composition	Fixing elements 1 rear panel
Material	steel
Color	Gray RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws captive - from the outside of enclosure
Height	Nominal 78.74 in (2000 mm)
Width	Nominal 15.75 in (400 mm)

### Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	00785901949770
Nbr. of units in pkg.	1
Package weight(Lbs)	30.8 lb(US) (13.97 kg)
Returnability	Yes
Country of origin	ES

### Packing Units

Package 1 Height	1.38 in (35.000 mm)
Package 1 width	14.76 in (375.000 mm)
Package 1 Length	82.09 in (2085.000 mm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---