



Main

Device short name	FDM128
Product or component type	Display module
Accessory / separate part category	Display and signalling accessory
Range compatibility	Masterpact MTZ Masterpact NW MasterPact NT ComPact NSX ComPact NS630b...1600 ComPact NS1600b...3200 PowerPact H PowerPact J PowerPact L PowerPact P PowerPact R Acti 9 Smartlink smart communication module
Product name	Enerlin'X FDM
Function of module	Remote control View network Metering Display alarm

Complementary

Control type	Remote control
Mounting mode	Flush mounting
Mounting support	Surface mount with kit
Display type	Active matrix colour TFT LCD with LED backlight
Display resolution	320 x 240 pixels QVGA
View angle horizontal x vertical	70 x 80°
[Us] rated supply voltage	24 V DC - 15...20 %
Maximum power consumption in W	6.8 W
Standards	CE CSA UL
Height	5.08 in (129 mm)
Width	6.42 in (163 mm)
Depth	2.22 in (56.5 mm)
Accessory / separate part category	Spare part ComPact NS630b...1600 Spare part ComPact NS1600b...3200

Environment

IP degree of protection	IP54 Front face IP65
Ambient air temperature for operation	14...131 °F (-10...55 °C)

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901386049
Nbr. of units in pkg.	1
Package weight(Lbs)	1.89 lb(US) (0.86 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	2.76 in (7.000 cm)
Package 1 width	7.17 in (18.200 cm)
Package 1 Length	10.63 in (27.000 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------