



## Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2GU
Product or component type	Switch-disconnector-fuse
Device application	Protection
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I <sub>th</sub> ] conventional free air thermal current	60 A 104 °F (40 °C)
[I <sub>e</sub> ] rated operational current	60 A
Fuse type	UL
Fuse size	J
Network type	DC AC
Network frequency	50/60 Hz

## Complementary

Type of operating handle	External frontal
Mounting support	Plate
[U <sub>i</sub> ] rated insulation voltage	750 V
[U <sub>imp</sub> ] rated impulse withstand voltage	8 kV
Rated operational power in W	30 KW 400 V 40 KW 500 V 55 kW 690 V
Short-circuit withstand	17.6 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit lugs-ring terminals 0.01...0.02 in <sup>2</sup> (6...16 mm <sup>2</sup> )
Tightening torque	Power circuit 30.98 lbf.in (3.5 N.m)

## Environment

Standards	CSA C22.2 No 4 UL98
IP degree of protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) body
Height	5.35 in (136 mm)
Width	5.88 in (149.3 mm)
Depth	4.84 in (123 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901547143
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8 lb(US) (1.72 kg)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.18 in (15.7 cm)
Package 1 width	7.01 in (17.8 cm)
Package 1 Length	9.06 in (23 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Weight	21.56 lb(US) (9.78 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Weight	107.38 lb(US) (48.708 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------