



## Main

Range	Thalassa
Accessory / separate part category	Fixing accessory
Product or component type	Wall fixing support
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Top and bottom, on rear of the enclosure
Range compatibility	Thalassa PLM
Device composition	Fixing screws 4 lug

## Complementary

Material	Polyamide 6 with 30 % fibre glass
Color	Gray RAL 7035)
Fixing mode	Screwed - from the outside
Permanent permissible load	220.46 Lb(US) (100 kg) horizontal position 440.92 lb(US) (200 kg) vertical position
Height	12.13 ln (308 mm) 16.93 ln (430 mm) 20.87 ln (530 mm) 25.47 ln (647 mm) 29.41 ln (747 mm) 33.35 ln (847 mm) 41.57 in (1056 mm)
Width	10.04 ln (255 mm) 12.99 ln (330 mm) 16.93 ln (430 mm) 17.17 ln (436 mm) 21.10 ln (536 mm) 25.04 ln (636 mm) 33.54 in (852 mm)

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901476788
Nbr. of units in pkg.	1
Package weight(Lbs)	0.66 lb(US) (0.30 kg)
Returnability	Yes
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	3.94 in (10 cm)
Package 1 Length	5.31 in (13.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>