

HIPPO HOPPER[®]



SELF-DUMPING HOPPERS

Manufactured by



www.hippohopper.com

713-466-3962 • 888-830-3962

CNC 90 Degree Self-Dumping Hopper

Hippo Hopper CNC 90 degree self-dumping hopper (2000 LB capacity)

The lowest CNC hopper on the market expressly designed for the collection of chips and shavings from very low chip conveyors. This hopper dumps to a full 90 degrees when attached to forklift. With casters included this hopper can easily be maneuvered in and out of tight spaces. Along with our standard 1/4 and 1/3 cubic yard model custom sizes can be built to meet your specific application.

- ✓ Water tight all welded 12 gauge carbon steel box.
- ✓ 3/16" formed fork pocket base and security strap
- ✓ Standard paint Industrial gray enamel, with optional colors available



Designed to fit under the lowest chip conveyor...

Roll-in, Roll-out and dump with fork truck.

MODEL	SIZE	Weight	L	W	H	LH	Fork Pocket
HH02-LBX90	1/4 CU YD	190 Lbs.	36"	48"	14"	14"	22" X 2 3/4
HH12-LBX90	1/3 CU YD	345 Lbs.	48"	48"	14"	14"	22" X 2 3/4

The **Hippo Hopper** self-dumping hopper is the fastest, safest, easiest and most economical way to load, transport and dump scrap and bulk material.

Hopper Sales: (832) 456-4516 or sales@hippohopper.com

Manufactured by FabCorp, Inc. - 6951
West Little York - Houston, Texas

