



### Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	1L
Length in 18 mm modules	24

### Complementary

Number of ways	24 ways 1 L
Poles configuration for 1 way	1 x 1P
Connection pitch	0.71 in (18 mm)
Connector type	Tooth
Distance between way	0.71 in (18 mm)
Marking	L
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	100 A 104 °F (40 °C)
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top or bottom tunnel type terminals Top or bottom on double terminal
9 mm pitches	48
Width	16.93 in (430 mm)
Color	White (RAL 9003)
Range compatibility	Acti 9 iC60 Acti 9 iK60 Acti 9 iID Acti 9 iID K Acti 9 iSW Acti 9 iSW-NA Multi 9 C60

### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	1760 °F (960 °C) 30 s ) IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

## Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	00785901952190
Nbr. of units in pkg.	1
Package weight(Lbs)	0.22 lb(US) (0.10 kg)
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.20 in (0.5 cm)
Package 1 width	1.18 in (3 cm)
Package 1 Length	16.81 in (42.7 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	2.46 lb(US) (1.118 kg)
Package 2 Height	2.44 in (6.2 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	18.39 in (46.7 cm)
Unit Type of Package 3	S04
Number of Units in Package 3	160
Package 3 Weight	41.03 lb(US) (18.613 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------