

# Product data sheet

## Characteristics

# RQC200SFMG

Meter mains, QO, combination service entrance, ringless socket, 200A, outdoor surface mount, no bypass



### Main

Product or component type	Meter Mains
Range of product	QO
Includes	Circuit breaker 1) 2P 200 A 120/240 V AC main supply ready assembled

### Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface outdoor)
Number of spaces	0
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil aluminium/copper)line side AWG 6...350 kcmil aluminium/copper)service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Marking	Florida metering group
Height	23.03 in (584.96 mm)
Width	24.04 in (610.62 mm)
Depth	4.67 in (118.62 mm)

### Environment

Product certifications	UL E-6294
------------------------	-----------

### Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901186397
Nbr. of units in pkg.	1
Package weight(Lbs)	31.35 lb(US) (14.22 kg)
Returnability	Yes

## Packing Units

Package 1 Height	6.90 in (17.526 cm)
Package 1 width	26.90 in (68.326 cm)
Package 1 Length	26.90 in (68.326 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>