


# 8501XDO40V62Y414

NEMA Control Relay, Type X, machine tool,  
10A resistive at 600 VAC, 4 normally open  
contacts, 115/125 VDC coil, pan head



## Main

Range	8501X
Relay Type	Control
Product	Relay
Current Rating	10 A AC 5 A DC

## Complementary

Coil Voltage	115/125 V DC
Control circuit voltage limits	Operational 0.8...1.1 U <sub>c</sub> DC
Rated breaking capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 10 A ≤ 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301...600 V DC inductive control circuit UL 508 4 A 125 V DC resistive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
[Icm] rated short-circuit making capacity	60 A 120 V AC inductive control circuit UL 508 30 A 240 V AC inductive control circuit UL 508 15 A 480 V AC inductive control circuit UL 508 12 A 600 V AC inductive control circuit UL 508 10 A ≤ 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301...600 V DC inductive control circuit UL 508 4 A 125 V DC inductive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Inrush power in W	18 W
Hold-in power consumption in W	18 W
Operating time	37 ms - pick-up 21 ms - drop-out
Contact Configuration	4 NO 4 standard contact cartridges
Electrical connection	Ring tongue
AWG gauge	AWG 18...AWG 12 copper
Tightening torque	Control circuit 9.03...12.04 lbf.in (1.02...1.36 N.m) screw terminals
Mounting Type	Panel
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	5.17 in (131.32 mm)

## Environment

Operating Temperature	-40...160 °F (-40...71 °C)
Certifications	UL listed file E78403 CCN NKCR CSA LR60905 class 3211 03

## Ordering and shipping details

Category	21157 - 8501 XDO (DC)
Discount Schedule	CP2
GTIN	00785901743385
Nbr. of units in pkg.	1
Package weight(Lbs)	3.35 lb(US) (1.52 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	8.89 in (22.581 cm)
Package 1 width	3.50 in (8.890 cm)
Package 1 Length	22.58 in (57.355 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------