

Product data sheet

Characteristics

MP44125

MP Meter Pak, main lugs, four ringed sockets, no bypass, 4 jaws, UG, OH, 400 A bus, 125 A, 240 VAC single phase



Main

Product	Meter Center
Socket Rating	125 A
Main Type	Main Lugs
Number of Jaws	4
Number of Meter Sockets	4
Socket Type	Ringed

Complementary

Main Rating	400 A
Bus Rating	400 A
Certifications	UL Listed
Type	Meter-Pak
Busbar Material	Aluminium busbar
Bypass Type	No bypass
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	240 V AC
Mounting	Surface
Phase	1 phase
Service Feed Location	OH UG
Wire Size	AWG 1/0...600 kcmil 1 aluminium AWG 1/0...600 kcmil 1 copper
Wire Configuration	3-wire
Height	48.12 in (1222.25 mm)
Width	24.34 in (618.24 mm)
Depth	7.28 in (184.91 mm)

Ordering and shipping details

Category	00021 - METER-PAK
Discount Schedule	DE4
GTIN	00785901001805
Nbr. of units in pkg.	7
Package weight(Lbs)	89.86 lb(US) (40.76 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	0.71 ft (0.216 m)
Package 1 width	2.06 ft (0.627 m)
Package 1 Length	4.11 ft (1.252 m)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------