

Protect It! 7-Outlet Surge Protector, 25 ft. Cord, 1080 Joules, Diagnostic LED, Light Gray Housing

MODEL NUMBER: TLP725



Safeguard your computer, printer, scanner, router, modem and other small home electronics against dangerous surges, spikes and line noise.

Description

Perfect for your home or office workstation, the TLP725 Protect It!® 7-Outlet Surge Protector features a surge protection rating of 1080 joules to defend your sensitive electronic components against strong surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges up to \$25,000 for life (valid in the U.S., Canada and Puerto Rico only).

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP725 protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). It also filters out electromagnetic interference (EMI) and radio frequency interference (RFI) that can disrupt your electronics and inflict hardware damage or data loss.

Your devices plug into seven NEMA 5-15R outlets, one of which is spaced apart to accept a bulky transformer without blocking adjacent outlets. An integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. The lighted on/off switch provides one-touch control over connected equipment. A diagnostic LED confirms your connected equipment is protected.

The extra-long 25-foot (7.6-meter) AC power cord with NEMA 5-15P plug gives you flexibility to reach distant outlets while fitting easily into your workstation or home theater setup. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the light gray plastic housing.

Features

1080-Joule Surge Protection for Home or Office Electronics Protects your computer, printer, scanner, router, modem and other small home electronics against even the strongest surges and spikes
Recommended for any desktop, network or home electronics application requiring AC line protection
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss
Exceeds IEEE 587 Category A and B surge suppression specifications

7 Outlets Accept Wide Range of Electronic Devices 7 NEMA 5-15R AC outlets accept most computers and peripherals
Special end outlet designed for bulky transformers without blocking other outlets

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment
Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
Diagnostic LED confirms protection status at a glance
Conforms to current UL 1449 3rd Edition safety standards
ABS fire retardant plastic case provides extra safety and durability

Fits Effortlessly Into Your Workstation Extra-long 25 ft. AC power cord with NEMA 5-15P plug reaches

Highlights

- 7 NEMA 5-15R outlets—one designed for a bulky transformer
- 1080-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 25 ft. AC power cord with NEMA 5-15P plug

Package Includes

- TLP725 Protect It! 7-Outlet Surge Protector, Light Gray Housing
- Owner's manual



distant outletsKeyhole slots on bottom panel provide convenient wall or desk mounting options
Backed by Tripp Lite's Ultimate Lifetime Insurance\$25,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332138316
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	25
Right-Angle Plug	No
Input Cord Length (m)	7.62
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns



Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Color (AC Line Cord)	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 151mm; Distance between slot height = 24mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	6.10 x 16.51 x 35.56
Shipping Dimensions (hwd / in.)	2.40 x 6.50 x 14.00
Shipping Weight (kg)	1.51
Shipping Weight (lbs.)	3.32
Unit Dimensions (hwd / cm)	3.35 x 5.21 x 29.69
Unit Dimensions (hwd / in.)	1.32 x 2.05 x 11.69
Unit Weight (kg)	1.38
Unit Weight (lbs.)	3.04
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	RoHS



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>