

MFC-7240

Print • Copy • Scan • Fax

Compact Laser All-in-One



Top Features:

Fast Printing & Copying

- Help increase your productivity with black print and copy speeds up to 21ppm

Flexible Paper Handling

- Adjustable, 250-sheet capacity paper tray for letter or legal-size paper. Manual feed slot for envelope printing.

20-page Capacity Auto Document Feeder

- Copy, scan or fax multi-page documents easily (up to legal-size paper)

High-Yield Replacement Toner Cartridge

- Help lower your operating costs with a high-yield 2,600-page[▼] replacement toner cartridge*

High-Quality Output

- Print professional reports, spreadsheets, and business documents

High-Quality Monochrome Scanning

- Up to 19200 x 19200 dpi (interpolated) resolution with a variety of “scan to” features

Standalone Copying and Faxing

- No PC required to use copy or fax functions.

Telephone Handset

- Auto Fax/Tel switching for receiving fax and voice calls on a single phone line

Fax Flexibility

- Send and receive faxes from the all-in-one or your computer[†]

Customer Support

- 1-year limited warranty with toll-free technical support for the life of your machine



* Additional purchase required

[▼] Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4)

[†] Black and white only. PC Fax Receive not available for Mac OS

Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	2-line mono / 16 characters
Paper Size (maximum)	Up to 8.5" x 14" (legal)
Print Speed (maximum)	Up to 21ppm
Print Resolution (maximum)	Up to 2400 x 600 dpi
Emulations	GDI
Memory (std./max.)	16MB / 16MB
Paper Input Capacity (maximum)[∞]	250-sheet capacity paper tray, single-sheet manual feed slot
Output Capacity (maximum)[∞]	100 sheets (face down), 1 sheet (face up)
Auto Document Feeder	Up to 20-pages
Standard Interfaces	Hi-Speed USB 2.0
Copy Speed (maximum)	Up to 21cpm
Copy Resolution (maximum)	300 x 600 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments
Copy Options	Sorting, N-in-1, Multi-copying (up to 99)
Scanner Type	Monochrome Sheetfed with ADF
Scan Resolution (maximum)	Optical: Up to 600 x 600 dpi Interpolated: Up to 19200 x 19200 dpi
Scan To Capability	File, Image, E-mail, OCR, File
Document Viewer / OCR Software	Nuance PaperPort® 12SE w/ OCR for Windows® Presto!(R) PageManager®9 w/OCR for Mac®
Fax Modem	14.4K bps
Fax Page Memory (maximum)²	Up to 400 pages
One Touch / Speed Dial Locations	22 / 200
PC Fax Capability⁺	Yes
Operating Systems Compatibility	Windows®: Windows®7 / Windows Vista® / XP / XP Professional x64 Mac®: Mac OS X v10.5.8, 10.6.x, 10.7.x Linux
Maximum Monthly Duty Cycle[◊]	Up to 10,000 pages
Recommended Monthly Volume[†]	Up to 250 to 2,000 pages
Warranty	1-year limited warranty

Supplies & Accessories*:

TN-420	Standard Yield Toner (approx. 1,200 pages) [▼]
TN-450	High-Yield Toner (approx. 2,600 pages) [▼]
DR-420	Drum Unit (approx. 12,000 pages) [^]
BP60MPLTR	Multi-Purpose Paper - Letter size (8.5" x 11", 500 sheets)

Setup Information:

UPC Code	012502633143
Unit Dimensions	14.7"W x 14.6"D x 12.2"H
Unit Weight	19.8 lbs.
Carton Dimensions	18.7"W x 18.0"D x 17.2"H
Carton Weight	26.5 lbs.
Pallet Quantity	8
Pallet Tiers	2
Pallet Quantity per Tier	4
Pallet Size	48" x 40"
Pallet + Cartons Height	39.3"
Pallet + Carton Weight	261.6 lbs.
Country of Origin	China
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

Brother™ MFC-7240
Starter Toner Cartridge (700 pages) [▼]
DR420 Drum Unit (12,000 Pages) [^]
Quick Setup Guide and Basic User's Guide
Documentation / Installation CD-ROM(s)
AC Power Cord
Telephone Line Cord



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com

* Additional purchase required
[∞] Maximum capacity based on using 20 lb. paper
² Using ITU-T Test Chart #1 with MMR coding and std. resolution
⁺ Black and white only. PC Fax Receive not available for Mac OS
[◊] Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

■ The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs
[▼] Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).
[^] Drum yield is approx., and may vary by type of use.

Scannable Barcode:

