

STAINLESS STEEL HYGENIC FLEX FITTING

Features:

- Type 316 stainless steel Straight, External Thread
- Food contact and hygienic conduit fitting for use with Hygienic Flex conduits
- Face Seal & Nut Seal = Polyester elastomer
- Conduit seal and insulated throat = Nylon PA6
- Color = Stainless steel, All plastic parts = Blue

Technical Properties:

- High tensile strength
- Oil resistant
- Corrosion resistant

Certifications and Compliances:

- NEMA 4X Approved
- ROHS

Applications:

Suitable for knockouts or threaded entries. Stainless Steel compression fitting comprising of nut, insert and nylon compression seal. Also ensures high mechanical strength.



Part Number	Trade Size (in)	A (in)	B (in)	C (in)	D (in)	E (in)
S60500FCHG	½	0.47	1.34	1.34	0.57	1.26
S60700FCHG	¾	0.55	1.39	1.57	0.74	1.50
S61000FCHG	1	0.59	1.52	1.87	0.97	1.75
S61200FCHG	1¼	0.63	1.67	2.32	1.29	2.17
S61500FCHG	1½	0.63	1.83	2.55	1.48	2.44
S62000FCHG	2	0.63	1.83	2.99	1.93	2.95

All dimensions are for informational purposes only *Tolerances +/- 5%

