

HEATEDGEAR

DEWALT



REALTREE XTRA® CAMOUFLAGE

DCHJ074



OUTER SHELL - Cotton, Polyester / INNER SHELL - Cotton, Polyester

Sizes: S, M, L, XL, 2X, 3X

Durable wind resistant polyester outer shell

3 core heating zones which include L&R chest and mid-back

Realtree® XTRA® Camouflage pattern in heavy-weight fleece

LED controller with 3 temperature settings (high, med, low with pre-heat function)

Battery pocket accepts 20V MAX* XR lithium-ion batteries which improves run time by up to 25%*

USB power source with USB power port for charging portable electronic devices (Extension allows you to place it in front or back pockets)


Includes battery fuel gauge

Two external front waist pockets,
One internal accessory pocket

Integrated drawstring hood

DCHJ074D1

Includes: DCHJ074 Heated Jacket, DCB092 USB Power Source, Charger and 20V Max* XR lithium-ion battery



*At maximum initial battery voltage, as compared to 1.5aHr DCB201

Copyright ©2017 DEWALT. DEWALT is a registered trademark of DEWALT Industrial Tool Co., used under license. All rights reserved. The yellow and black color scheme is a trademark for DEWALT Power Tools and Accessories. Trademark License: Radians, Inc., Memphis, TN 38141, 877-723-4267, www.radians.com. A licensee of DEWALT Industrial Tool Co.

GUARANTEED TOUGH.™



RADIANS, INC. • 5305 Distriplex Farms Drive • Memphis, TN 38141
Toll Free 877-RADIANS • Fax 901-266-2558 • www.radians.com

DCHJ074-SSH_Rev00 081017