

## DCHJ075





**OUTER SHELL - Polyester / INNER SHELL - Polyester** 

Sizes: S, M, L, XL, 2X, 3X

Durable water and wind resistant polyester outer shell

3 core heating zones which include L&R chest and mid-back

LED controller with 3 temperature settings (high, med, low with pre-heat function)

Battery pocket accepts 20V MAX\* XR lithium-ion batteries which improves run time by up to 25%\*

USB power source with USB power port for charging portable electronic devices (Extension allows you to place it in front or back pockets)

Includes battery fuel gauge

Reflective piping and zipper for increased visibility

2 Slash, zip pockets

1 Internal accessory pocket







DCHJ075D1
Includes: DCHJ075 Heated Jacket,
DCB203 20V MAX\* Lithium-Ion Battery (2.0 Ah),
Charger and DCB092 USB Power Source











\*At maximum initial battery voltage, as compared to 1.5aHr DCB201

Copyright ©2017 DEWALT. DEWALT. DEWALT is a registered trademark of DEWALT Industrial Tool Co., used under license. All rights reserved. The yellow and black color scheme is a trademark for DEWALT Power Tools and Accessories. Trademark License: Radians, Inc., Memphis, TN 38141, 877-723-4267, www.radians.com. A licensee of DEWALT Industrial Tool Co.

**GUARANTEED TOUGH**:

