

# Detectable Marking Tape - Green Sewer Line

---



## DESCRIPTION

**Black Swan's Detectable Marking Tape** is a superior detectable marking tape used for location and early warning protection for non-metallic underground lines. The solid aluminum core is encased between two layers of plastic with an overall thickness of 5 mil (.005"). With proper detection equipment this tape is easily located. All printing is encapsulated in the tape providing a permanence of message.

## DIRECTIONS

For best results shallow bury tape 6" - 12" from finished grade, ensuring maximum distance between warning tape and buried pipe.

---

**UPC NUMBER AND CARTON INFORMATION**

| <b>STOCK NO.</b>         | <b>SIZE</b> | <b>UPC NUMBER</b> | <b>CARTON CUBIC FEET</b> |
|--------------------------|-------------|-------------------|--------------------------|
| <b>Blue Water Line</b>   |             |                   |                          |
| 15250                    | 2" x 1000'  | 0 54647 15250 9   | 1.204                    |
| 15255                    | 3" x 1000'  | 0 54647 15255 4   | 1.204                    |
| 15260                    | 6" x 1000'  | 0 54647 15260 8   | 1.1875                   |
| <b>Green Sewer Line</b>  |             |                   |                          |
| 15270                    | 2" x 1000'  | 0 54647 15270 7   | 1.204                    |
| 15275                    | 3" x 1000'  | 0 54647 15275 2   | 1.204                    |
| 15280                    | 6" x 1000'  | 0 54647 15280 6   | 1.1875                   |
| <b>Red Electric Line</b> |             |                   |                          |
| 15290                    | 2" x 1000'  | 0 54647 15290 5   | 1.204                    |
| 15295                    | 3" x 1000'  | 0 54647 15295 0   | 1.204                    |
| 15300                    | 6" x 1000'  | 0 54647 15300 1   | 1.1875                   |
| <b>Yellow Gas Line</b>   |             |                   |                          |
| 15310                    | 2" x 1000'  | 0 54647 15310 0   | 1.204                    |
| 15315                    | 3" x 1000'  | 0 54647 15315 5   | 1.204                    |
| 15320                    | 6" x 1000'  | 0 54647 15320 9   | 1.1875                   |