



Model XSH08Z Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty	Unit
001	266326-2	TAPPING SCREW 4X18	1	PC.
002	458750-5	FRONT GRIP	1	PC.
006	855P90-2	XSH08 NAME PLATE	1	
007	266326-2	TAPPING SCREW 4X18	8	PC.
008	183K66-2	HANDLE SET	1	PC.
	C10 263005-3	RUBBER PIN 6	4	PC.
	C20 818C43-4	CAUTION LABEL	1	PC.
	D10	INC. 20		
010	812G25-2	INDICATION LABEL	1	PC.
011	620983-4	CONTROLLER COMPLETE	1	PC.
	D10	INC. 10		
012	419704-7	LOCK OFF BUTTON	1	PC.
013	231433-0	COMPRESSION SPRING 4	2	PC.
014	458594-3	SWITCH LEVER	1	PC.
015	632M92-5	SWITCH UNIT	1	PC.
016	651083-9	SWITCH C3XA-1PSPM	1	PC.
017	643874-2	TERMINAL	2	PC.
018	855P94-4	XSH08 SERIAL NO. LABEL	1	
019	911243-8	PAN HEAD SCREW M5X25	3	PC.
020	183K66-2	HANDLE SET	1	PC.
	C10 263005-3	RUBBER PIN 6	4	PC.
	C20 818C43-4	CAUTION LABEL	1	PC.
	D10	INC. 8		
021	458746-6	MOTOR HOUSING	1	PC.
022	911258-5	PAN HEAD SCREW M5X35	4	PC.
023	629375-4	STATOR	1	PC.
024	458749-0	BAFFLE PLATE	1	PC.
025	266326-2	TAPPING SCREW 4X18	2	PC.
026	620936-3	LED CIRCUIT	1	PC.
027	458751-3	LIGHT COVER	1	PC.
028	266326-2	TAPPING SCREW 4X18	1	PC.
029	257953-6	BOW STOP RING E-12	1	PC.
030	271447-7	LEVER 110	1	PC.
031	252262-8	COLLERED HEX. NUT M8	1	PC.
032	519534-7	ROTOR ASSY	1	PC.
	D10	INC. 33,35		
033	210022-4	BALL BEARING 626DDW	1	PC.
035	210059-1	BALL BEARING 6000DDW	1	PC.
036	251529-1	+ PAN HEAD SCREW M4X14	1	PC.
037	347441-2	SHAFT LOCK	1	PC.
038	232381-6	COMPRESSION SPRING 6	1	PC.
039	286039-9	CAP	1	PC.
040	140D80-9	BLADE CASE COMPLETE	1	PC.
	C10 213434-0	O RING 26	1	PC.
	C20 818C47-6	SCALE LABEL	1	PC.
041	266396-1	FLATHEAD SQUARENECKBOLT M8X24	1	PC.
042	262185-2	RUBBER SLEEVE8	1	PC.
043	251572-0	+ COUNTERSUNK HEAD SCREW M6X30	1	PC.
044	211031-6	BALL BEARING 608ZZ	1	PC.

045	961057-5	RETAINING RING S-17	1 PC.
046	226838-7	HELICAL GEAR 37	1 PC.
047	257451-0	RING 17	1 PC.
048	285809-3	BEARING RETAINER 23-36	1 PC.
049	210301-0	BALL BEARING 6003DDW	1 PC.
050	327192-3	SPINDLE	1 PC.
051	213565-5	O RING 42	1 PC.
052	136021-7	BEARING BOX ASSY	1 PC.
	D10	INC. 51	
053	265034-2	+ COUNTERSUNK HEAD SCREW M5X16	2 PC.
054	232467-6	TENSION SPRING 4	1 PC.
055	319740-2	SAFETY COVER	1 PC.
056	271450-8	LEVER 37	1
057	265178-8	PAN HEAD SCREW M4X16	1 PC.
058	267337-0	FLAT WASHER 40	1 PC.
059	257452-8	RETAINING RING (EXT) WR-40	1 PC.
060	224594-3	INNER FLANGE 35	1 PC.
061	224409-4	OUTER FLANGE 35	1 PC.
062	266283-4	HEX. SOCKET HEX. BOLT M8X20	1 PC.
063	347532-9	DEPTH GUIDE	1
064	251920-3	CAP SQUARE NECK BOLT M6X30	1 PC.
065	265118-6	+ PAN HEAD SCREW M5	1 PC.
066	319829-6	FRAME	1
067	911516-9	PAN HEAD SCREW M4X12	2 PC.
068	252103-8	HEX. LOCK NUT M5-8	1 PC.
069	251267-5	+ PAN HEAD SCREW M6	1 PC.
070	213026-5	O RING 7	1 PC.
071	319827-0	STOPPER	1
072	263041-9	SHOULDER PIN 3-5	1
073	231234-6	COMPRESSION SPRING 3.5	1 PC.
074	419632-6	POSITION PLATE	1 PC.
075	911118-1	PAN HEAD SCREW M4X12	1 PC.
076	319830-1	FRONT ANGULAR PLATE	1
077	266559-9	H.S.BUTTON HEAD BOLT M6X4	1 PC.
078	253111-2	FLAT WASHER 6	1 PC.
079	265776-8	THUMB SCREW M6X26	1 PC.
080	252270-9	THUMB NUT M6	1
081	253111-2	FLAT WASHER 6	1 PC.
082	319831-9	REAR ANGULAR PLATE	1
083	266559-9	H.S.BUTTON HEAD BOLT M6X4	1 PC.
084	231234-6	COMPRESSION SPRING 3.5	1 PC.
085	263041-9	SHOULDER PIN 3-5	1
086	265775-0	THUMB SCREW M4X3	1 PC.
087	419627-9	HOLDER	1 PC.
088	458092-7	SLIDE LEVER	1 PC.
089	253932-2	WAVE WASHER 10	1 PC.
090	345977-5	PLATE	1 PC.
091	265701-9	THUMB SCREW M6X14	1 PC.
092	233376-2	COMPRESSION SPRING 8	1 PC.
093	265775-0	THUMB SCREW M4X3	1 PC.
094	419627-9	HOLDER	1 PC.
095	265174-6	+ TRUSS HEAD SCREW M4X16	2 PC.
096	319828-8	BASE	1
097	266225-8	H.S.SET SCREW(FLAT POINT)M6X8	3 PC.
098	345748-0	LOCK WASHER	1 PC.
099	912112-6	COUNTERSUNK HEAD SCREW M4X10	1 PC.

100	265174-6	+ TRUSS HEAD SCREW M4X16	2 PC.
A02	196520-1	DUST NOZZLE SET	1 PC.
C10	911128-8	P.H.SCREW M4X16 WITH WR	1 PC.
A03	783204-6	HEX. WRENCH 6	1 PC.
A04	B-61656	TCT BLADE185X24T WOOD	1 PC.