



Model XSH10Z Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty Unit
001	266326-2	TAPPING SCREW 4X18	1 PC.
002	459828-7	FRONT GRIP	1
003	140F99-0	CAP COMPLETE	1 PC.
	C10 213218-6	O RING 16	1 PC.
	C20 818H07-8	CAP LABEL	1 PC.
004	856L72-3	XSH10 NAME PLATE	1
005	266326-2	TAPPING SCREW 4X18	8 PC.
006	183N74-1	HANDLE SET	1
	C10 263005-3	RUBBER PIN 6	4 PC.
	C20 8004T4-4	CAUTION LABEL	1
	D10	INC. 18	
008	813T74-0	INDICATION LABEL	1 PC.
009	620C59-5	CONTROLLER COMPLETE	1
	D10	INC. 8	
010	419704-7	LOCK OFF BUTTON	1 PC.
011	231433-0	COMPRESSION SPRING 4	2 PC.
012	459829-5	SWITCH LEVER	1
013	632M92-5	SWITCH UNIT	1 PC.
014	651083-9	SWITCH C3XA-1PSPM	1 PC.
015	643874-2	TERMINAL	2 PC.
016	856L78-1	XSH10 SERIAL NO. LABEL	1
017	911243-8	PAN HEAD SCREW M5X25	3 PC.
018	183N74-1	HANDLE SET	1
	C10 263005-3	RUBBER PIN 6	4 PC.
	C20 8004T4-4	CAUTION LABEL	1
	D10	INC. 6	
019	459823-7	MOTOR HOUSING	1
020	266326-2	TAPPING SCREW 4X18	1 PC.
021	911258-5	PAN HEAD SCREW M5X35	4 PC.
022	629462-9	STATOR	1
023	459826-1	BAFFLE PLATE	1
024	266326-2	TAPPING SCREW 4X18	2 PC.
025	620936-3	LED CIRCUIT	1 PC.
026	459827-9	LIGHT COVER	1
027	266326-2	TAPPING SCREW 4X18	1 PC.
028	257953-6	BOW STOP RING E-12	1 PC.
029	271453-2	LEVER 132	1
030	252262-8	COLLERED HEX. NUT M8	1 PC.
031	519602-6	ROTOR ASS'Y	1
	D10	INC. 32,33	
032	210022-4	BALL BEARING 626DDW	1 PC.
033	210059-1	BALL BEARING 6000DDW	1 PC.
034	251529-1	+ PAN HEAD SCREW M4X14	1 PC.
035	347575-1	SHAFT LOCK	1
036	286039-9	CAP	1 PC.
037	233084-5	COMPRESSION SPRING 6	1 PC.
038	319860-2	BLADE CASE COVER	1
039	266034-5	TAPPING SCREW CT 4X16	4 PC.
040	136173-4	DUST NOZZLE ASS'Y	1

	D10	INC. 41	
041	213444-7	O RING 30	1 PC.
042	232227-6	LEAF SPRING	2 PC.
043	263005-3	RUBBER PIN 6	1 PC.
044	140P84-3	BLADE CASE COMPLETE	1
	C10	213434-0	O RING 26
	C20	8004T2-8	SCALE LABEL
045	266396-1	FLATHEAD SQUARENECKBOLT M8X	1 PC.
046	232563-0	TENSION SPRING 4	1
047	162686-9	OPEN LEVER	1
048	265A60-7	+ PAN HEAD SCREW M5X14	1
049	210029-0	BALL BEARING 608ZZ	1 PC.
050	961057-5	RETAINING RING S-17	1 PC.
051	226934-1	HELICAL GEAR 46	1
052	257451-0	RING 17	1 PC.
053	285809-3	BEARING RETAINER 23-36	1 PC.
054	210301-0	BALL BEARING 6003DDW	1 PC.
055	213623-7	O RING 46	1 PC.
056	136192-0	BEARING BOX ASS'Y	1
	D10	INC. 55	
057	265034-2	+ COUNTERSUNK HEAD SCREW M5.	2 PC.
058	327192-3	SPINDLE	1 PC.
059	232562-2	TENSION SPRING 6	1 PC.
060	319861-0	SAFETY COVER	1
061	459830-0	SPACER	1
062	267337-0	FLAT WASHER 40	1 PC.
063	257452-8	RETAINING RING (EXT) WR-40	1 PC.
064	224603-8	INNER FLANGE 40	1
065	224600-4	OUTER FLANGE 38	1
066	265A59-2	HEX.SOCKET HEAD BOLT M8	1
067	911113-1	PAN HEAD SCREW M4X10 WITH WR	1 PC.
068	271451-6	LEVER 55	1
069	252275-9	HEX. NUT M4-16	1
070	265A82-7	HEX. SOCKET HEAD SCREW M3X4	1
071	347576-9	OPEN PLATE	1
072	347577-7	WASHER 6	1
073	265135-6	+ COUNTERSUNK HEAD SCREW M4.	1 PC.
074	262185-2	RUBBER SLEEVE8	1 PC.
075	251572-0	+ COUNTERSUNK HEAD SCREW M6.	1 PC.
076	265776-8	THUMB SCREW M6X26	1 PC.
077	253111-2	FLAT WASHER 6	2 PC.
078	319865-2	FRONT ANGULAR PLATE	1
079	263041-9	SHOULDER PIN 3-5	1
080	231234-6	COMPRESSION SPRING 3.5	1 PC.
081	266559-9	H.S.BUTTON HEAD BOLT M6X4	1 PC.
082	450704-8	DIAL 27	1 PC.
083	251370-2	+ PAN HEAD SCREW M5	1 PC.
084	251528-3	+ PAN HEAD SCREW M6	1 PC.
085	257580-9	SLEEVE 8	1 PC.
086	266229-0	H.S.SET SCREW(CUP POINT)M5X8	1 PC.
087	911118-1	PAN HEAD SCREW M4X12	1 PC.
088	419632-6	POSITION PLATE	1 PC.
089	216008-6	STEEL BALL 4	1 PC.
090	233314-4	COMPRESSION SPRING 4	1 PC.
091	347574-3	DEPTH GUIDE	1
092	140P89-3	FRAME COMPLETE	1

C10	233025-1	COMPRESSION SPRING 2	2 PC.
C20	259008-3	PUSH NUT 4	2 PC.
C30	286041-2	CAP 14	2 PC.
C40	345747-2	SPACER PLATE	2 PC.
C50	347392-9	PLATE	2 PC.
093	252014-7	HEX. LOCK NUT M6-10	1 PC.
094	265A83-5	H.S.SET SCREW(FLAT POINT)M5X20	1
095	233025-1	COMPRESSION SPRING 2	1 PC.
096	412210-1	SLIDER	1
097	265A84-3	PAN HEAD SCREW M4X12 WITH WR	2
098	266332-7	R.H SQUARE NECK BOLT M6X35	1 PC.
099	319866-0	REAR ANGULAR PLATE	1
100	253111-2	FLAT WASHER 6	1 PC.
101	252270-9	THUMB NUT M6	1
102	263041-9	SHOULDER PIN 3-5	1
103	231234-6	COMPRESSION SPRING 3.5	1 PC.
104	266559-9	H.S.BUTTON HEAD BOLT M6X4	1 PC.
105	265701-9	THUMB SCREW M6X14	2 PC.
106	233376-2	COMPRESSION SPRING 8	2 PC.
107	265775-0	THUMB SCREW M4X3	2 PC.
108	419627-9	HOLDER	2 PC.
109	458092-7	SLIDE LEVER	2 PC.
110	253932-2	WAVE WASHER 10	2 PC.
111	345977-5	PLATE	2 PC.
112	345748-0	LOCK WASHER	2 PC.
113	912112-6	COUNTERSUNK HEAD SCREW M4X1	2 PC.
114	266225-8	H.S.SET SCREW(FLAT POINT)M6X8	2 PC.
115	319862-8	BASE	1
116	265181-9	+TRUSS HEAD SCREW M5X20	4 PC.
117	253811-4	FLAT WASHER 5	1 PC.
A01	162687-7	SUB BASE	1
A02	783204-6	HEX. WRENCH 6	1 PC.
A03	E-01965	TCT BLADE 235X24T WOOD EFFICU	1 PC.