



## Model XWT07Z Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty	Unit	
001	251476-6	H.S.H.BOLT M5X35 WITH WR	4	PC.	
004	851K73-0	XWT07 NAME PLATE	1		
005	266326-2	TAPPING SCREW 4X18	9	PC.	
006	183C08-8	HOUSING SET	1		
	D10	INC. 43			
007	620351-1	LED CIRCUIT	1	PC.	
008	456268-0	F/R CHANGE LEVER	1		
009	143416-7	SWITCH COMPLETE	1	PC.	
010	143417-5	SWITCH PLATE COMPLETE	1	PC.	
011	183C12-7	BATTERY HOUSING SET	1	SET	
	C10	263005-3	RUBBER PIN 6	2	PC.
	D10	INC. 46			
012	268284-8	PIN 1.5	1	PC.	
013	263036-2	RUBBER PIN 5	1	PC.	
014	424773-5	CUSHION RUBBER	1		
015	643899-6	TERMINAL	1	PC.	
020	424775-1	BUMPER	1		
021	143411-7	HAMMER CASE COMPLETE	1	PC.	
022	346948-5	WASHER 25	1		
023	231920-9	RING SPRING 16	1	PC.	
024	135716-9	ANVIL E ASS'Y	1	PC.	
	D10	INC. 23			
025	326612-4	HAMMER	1	PC.	
026	216002-8	STEEL BALL 4.8	29	PC.	
027	267493-6	FLAT WASHER 38	1		
028	234383-8	COMPRESSION SPRING 38	1	PC.	
029	216009-4	STEEL BALL 7.1	2	PC.	
030	227391-6	SPUR GEAR 24	3	PC.	
031	326611-6	SPINDLE	1	PC.	
032	268079-9	PIN 5	3	PC.	
033	267494-4	FLAT WASHER 25	1		
034	346947-7	RETAINER	1		
035	227392-4	INTERNAL SPUR GEAR 54	1	PC.	
036	213720-9	O RING 67	1	PC.	
037	135718-5	INTERNAL GEAR CASE ASS'Y	1	PC.	
	D10	INC. 36,38			
038	213961-7	O RING 22	1	PC.	
039	519384-0	ROTOR ASS'Y	1	PC.	
	D10	INC. 40,41			
040	210069-8	BALL BEARING 6900DDW	1	PC.	
041	211022-7	BALL BEARING 607ZZ	1	PC.	
042	629170-2	STATOR COMPLETE	1	PC.	
043	183C08-8	HOUSING SET	1		
	D10	INC. 6			
044	424773-5	CUSHION RUBBER	1		
045	424517-3	CUSHION	1	PC.	
046	183C12-7	BATTERY HOUSING SET	1	SET	
	C10	263005-3	RUBBER PIN 6	2	PC.
	D10	INC. 11			
047	346949-3	HOOK	1		
048	251314-2	+ SCREW M4X12	2	PC.	