



Model XVJ01Z Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty	Unit
001	187703-4	HOUSING SET	1	
	C10 263005-3	RUBBER PIN 6	2	PC.
	C20 801V48-5	SWITCH LABEL	2	
	C30 801X66-5	CAUTION LABEL	1	
	D10	INC. 4		
002	265995-6	TAPPING SCREW 4X18	7	PC.
003	853L43-1	XVJ01 NAME PLATE	1	
004	187703-4	HOUSING SET	1	
	C10 263005-3	RUBBER PIN 6	2	PC.
	C20 801V48-5	SWITCH LABEL	2	
	C30 801X66-5	CAUTION LABEL	1	
	D10	INC. 1		
007	632A96-5	SWITH UNIT	1	
008	266034-5	TAPPING SCREW CT 4X16	4	PC.
009	142112-4	GEAR HOUSING COVER COMPLETE	1	PC.
010	326302-9	SAFETY WIRE	1	
011	911104-2	PAN HEAD SCREW M4X6	1	PC.
012	454483-0	TOOL OPENER	1	
013	265026-1	+ PAN HEAD SCREW M4	1	PC.
014	231659-4	TORSION SPRING 6	1	PC.
015	346687-7	LINEAR GUIDE	1	PC.
016	232207-2	LEAF SPRING	1	PC.
017	911111-5	PAN HEAD SCREW M4X10 WITH W	4	PC.
018	256117-9	PIN 4	1	PC.
019	214031-5	PLANE BEARING 4	1	PC.
020	961017-7	STOP RING E-3	1	PC.
021	310548-7	SLIDER	1	PC.
022	268090-1	PIN 4	1	PC.
023	442195-7	GASKET	1	
024	267854-0	CAP WASHER 8	1	
025	421815-6	DUST SEAL 8	1	PC.
026	267854-0	CAP WASHER 8	1	
027	424569-4	DUST COVER	1	
028	962063-3	RETAINING RING R-13	1	PC.
029	165724-6	ROD	1	PC.
030	257347-5	RING 21	1	
031	233591-8	TORSION SPRING 10	1	PC.
032	233314-4	COMPRESSION SPRING 4	1	PC.
033	310485-5	LOCK PIN	1	PC.
034	310547-9	BLADE HOLDER	1	PC.
035	256528-8	PIN 2	1	PC.
036	961002-0	RETAINING RING S-6	1	PC.
037	253715-0	FLAT WASHER 6	1	PC.
038-1	212092-9	NEEDLE BEARING 407	1	
039	142109-3	GEAR COMPLETE	1	PC.
040	313260-8	BALANCE PLATE	1	
041	346688-5	PUSH PLATE	1	PC.
042	253196-8	FLAT WASHER 6	1	PC.
043	454484-8	SEAL PLATE	1	

044-1	272280-0	LEVER 17	1
045	233139-6	COMPRESSION SPRING 3	1 PC.
046	286032-3	CAP 5	1 PC.
047	268063-4	PIN 4	1 PC.
048	142111-6	GEAR HOUSING COMPLETE	1 PC.
049	961018-5	STOP RING E-5	1 PC.
050	210059-1	BALL BEARING 6000DDW	1 PC.
051	519329-8	ROTOR ASS'Y	1 PC.
	D10	INC. 50,52	
052	210022-4	BALL BEARING 626DDW	1 PC.
053	266490-9	TAPPING SCREW PT 2X6	3 PC.
054	629996-2	STATOR	1 PC.
055	620214-1	CONTROLLER	1
056	643899-6	TERMINAL	1 PC.
057	252171-1	SQUARE NUT M5-8	1 PC.
058	142110-8	RETAINER COMPLETE	1 PC.
059	319016-7	BASE	1
060	345237-5	CRANK PLATE	1 PC.
061	922231-0	HEX. SOCKET HEAD BOLT M5X20	1 PC.
062	232208-0	LEAF SPRING	1 PC.
063	346685-1	BASE PLATE	1
064	265085-5	+ COUNTERSUNK HEAD SCREW M4X8	4 PC.
065	135602-4	ROD ASS'Y	1 PC.
	D10	INC. 27-29,31-35	
A02	415524-7	ANTI-SPLINTERING DEVICE	1 PC.
A03	417852-6	COVER PLATE	1 PC.
A04	792473-8	JIGSAW BLADE NO.B22	1
A05	792529-7	JIG SAW BLADE B-10 US	1
A06	792729-9	JIGSAW BLADE NO.BR13	1
A07	783202-0	HEX. WRENCH 4	1 PC.