

VF 719

ECONOMY GRADE UPVC FILM TAPE

TYPICAL APPLICATIONS

- For sealing cartons with recycled fiber content, heavy ink coverage or rough surfaces

PRODUCT FEATURES

- Performs when subfreezing temperatures and moisture are factors
- High tack
- Use with a hand dispenser

CONSTRUCTION

Overall Grade/Function: Economy

Backing: Unplasticized polyvinylchloride (UPVC) film

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm

STANDARD LENGTH(S)

50 m


Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment.

Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	23 lbs/in width	40.3 N/10 mm
Adhesion to Stainless Steel	13 oz/in width	1.42 N/10 mm
Thickness	1.9 mils	0.048 mm
Elongation	60%	60%
Service Temperature Range	0 F to 150 F	-18 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

