

CP 20

Shurtape®
TRUE TO YOUR WORK™

8-DAY ShurRELEASE® PAINTER'S TAPE – MULTI-SURFACE

TYPICAL APPLICATIONS

- For masking painted surfaces, wood and metal
- Also used for holding plastic or paper drop cloths
- Not for use in lacquer applications or on anodized aluminum

PRODUCT FEATURES

- Medium adhesion
- UV-resistant
- Flexible and conformable
- Resists paint bleed
- High shear values and consistent surface contact for secure holding power
- Durable
- Removes cleanly for up to 8 days without surface damage

CONSTRUCTION

Overall Grade/Function: Multi-surface

Backing: Crepe paper

Adhesive: Rubber-based

STANDARD WIDTH(S)

24 mm 36 mm 48 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	24 lbs/in width	42.0 N/10 mm
Adhesion to Stainless Steel	32 oz/in width	3.50 N/10 mm
Thickness	5.7 mils	0.14 mm
Elongation	10%	10%
Service Temperature Range	50 F to 150 F	10 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

