

Single Control Lavatory Faucet

- | | |
|------------------------------------------------|------------------------------------------------|
| LF-M42-YPOC Finish(C) <input type="checkbox"/> | LF-O42-YPOC Finish(C) <input type="checkbox"/> |
| LF-M42-YPOU Finish(U) <input type="checkbox"/> | LF-O42-YPOU Finish(U) <input type="checkbox"/> |
| LF-M42-YPOY Finish(Y) <input type="checkbox"/> | LF-O42-YPOY Finish(Y) <input type="checkbox"/> |



- Single Control
- 1 or 3-Hole Installation
- Pforever Seal
- Solid Brass Construction

Specifications

Features

- 1.2 GPM Flow Rate
- Solid Brass Construction
- Temperature Memory Feature Retains Desired Temperature Setting
- Lever Handle
- Includes Metal Supply Nuts
- Accommodates Up to 2 1/2" of Finishing Material
- 1 or 3-Hole Installation; Deck Plate or Single Hole Mounting Option
- Metal Pop-Up
- Waterfall Trough Spout
- Pforever Seal Ceramic Disc Valve
- Pforever Warranty®

Code Compliance

Pfister products are designed and manufactured in compliance with the following standards and codes:

- IAPMO Certified
- CSA B125 Certified
- ASME A112.18.1
- NSF 61/9 Annex G (Low lead)
- Cal Green Compliant
- EPA WaterSense Certification 1.2 gpm, 4.5 L/Min
- ADA Compliant-ANSI A117.1 (Lever handles only)



Dimensions

