



Hard Coat 19

High Gloss Floor Finish

Hard Coat 19 is a dynamically energized polymer floor coating for virtually all floors and floor maintenance programs. Deep rich, clear glossy appearance. Durable and mark resistant, use as a seal and finish or recoat over existing floors. Excellent mark resistance, yet extremely buffable with extended wear and performance. Hard Coat 19 provides long-lasting brilliance on all resilient tile, synthetic, rubber, linoleum, and terrazzo floors. It will withstand repeated buffing and burnishing including propane machines.

DIRECTIONS

Read the entire label and SDS for proper use, handling and storage before using this product.

Application: For best results, floors should be clean and/or old coatings removed and the floor neutralized.

1. Apply finish in full uniform coats.
2. Allow to dry before recoating.
3. For maximum performance, apply additional coats of finish until the desired level of appearance and protection is achieved.
4. Allow to dry thoroughly for several hours before reopening up area for traffic.

Buffing: This finish can be spray buffed or high speed buffed/burnished. Follow directions of buffing compound.

Stripping: This finish can be removed using a high quality Nycoco stripping solution.



FAST FACTS

- High performance
- Brilliant gloss and appearance
- Use with any buffing/burnishing and floor maintenance program
- Reduces maintenance costs
- Durable, mark resistant

MARKETS

- Building Service Contractors
- Retail
- Education
- Healthcare
- Hospitality & Lodging

SPECIFICATIONS

Color	Opaque White
Scent	Acrylic
pH	8.0 - 9.0
Solid Content	19%

Slip Resistance is greater than 0.5% coefficient of friction. Meets or exceeds ASTM D-2047.

PACKAGING

NL167-G4	4x1 Gallons/Case
NL167-P5	5 Gallon Pail
NL167-D30	30 Gallon Drum
NL167-D55	55 Gallon Drum

Nycoco Products Company

800.752.4754

nycoproducts.com

© NPC FF.NL167.032513

Refer to SDS for more information.