

# No-Hub Couplings



## DESCRIPTION

**Black Swan's No-Hub Couplings** are high quality no-hub couplings. Gasket is made of 100% neoprene and complies with ASTM C 564. Clamp is made of stainless steel. UPC Approved.

Ideal for underground or above ground use.

For best results, use **Black Swan's No-Hub Sealant** when making installation.

---

## DIRECTIONS

1. Place gasket on end of one pipe push pipe in firmly.
  2. Place second pipe into gasket and pack in firmly.
  3. Make sure both pipes are aligned properly.
  4. Slide clamp over the gasket so the gasket is completely covered.
  5. Use a calibrated torque wrench and tighten the stainless steel screws alternatively to the proper torque pounds (60 inch pounds).
- 

## CAUTION

**CAUTION!** Harmful if taken internally. Non-Flammable.

---

### UPC NUMBER AND CARTON INFORMATION

<b>STOCK NO.</b>	<b>SIZE</b>	<b>UPC NUMBER</b>	<b>CARTON CUBIC FEET</b>
21110	1-1/2"	0 54647 21110 7	1.05
21120	2"	0 54647 21120 6	1.39
21130	3"	0 54647 21130 5	2.49
21140	4"	0 54647 21140 4	3.42
21150	5"	0 54647 21150 3	2.26
21160	6"	0 54647 21160 2	2.71
21180	8"	0 54647 21180 0	3.19
21190	10"	0 54647 21190 9	3.74
21220	2" x 1-1/2"	0 54647 21220 3	1.32
21230	3" x 2"	0 54647 21230 2	2.55
21240	4" x 2"	0 54647 21240 1	2.61
21250	4" x 3"	0 54647 21250 0	2.61