

Concentrate
Makes up to 32 Gallons



Deodorizer • Disinfectant
Mildewstat • Virucide* • Sanitizer



Original
Eucalyptus
Scent

- Multi-Purpose Cleaner
- Kill Viruses* in 60 Seconds
- Kills 99.99% of Germs[†] in 60 Seconds
- Air Freshener • Laundry Refresher

Active Ingredients:
Alkyl (C₁₄ 50%, C₁₂ 40%, C₁₆ 10%)
dimethyl benzyl ammonium chloride... 2.00%
Inert Ingredients 98.00%
Total 100.00%

Item#	Packaging	Shipping Wt. (lbs.)	Cube Size (ft. ³)
911062-G4	4x1 Gallon	36	1.20
911062-5G	1x5 Gallon	45	1.35
911062-35G	1x35 Gallon	310	7.40
911062-55G	1x55 Gallon	480	10.70



EPA Reg. No. 66243-2, EPA Est. No. 66243-GA-1

Clean Control Corporation
Made in the USA
PO Box 7444 • Warner Robins GA 31095
Quality Assurance Hotline 800.841.3904
9:00am-4:00pm Mon.-Fri. (EST)
odobanprofessional.com



Deodorizer • Disinfectant Mildewstat • Virucide* • Sanitizer

It is a violation of Federal Law to use this product in a manner inconsistent with its labeling. This product is not to be used as a terminal sterilant/high level disinfectant on any surface or instrument that (1) is introduced directly into the human body, either into or in contact with the bloodstream or normally sterile areas of the body, or (2) contacts intact mucous membranes but which does not ordinarily penetrate the blood barrier or otherwise enter normally sterile areas of the body. This product may be used to preclean or decontaminate critical or semi-critical medical devices prior to sterilization or high-level disinfection.

DIRECTIONS FOR USE

WHERE TO USE

OdoBan® use-solutions are noncorrosive and nonstaining to plastic, vinyl, synthetics, enamel, tile and most common metals. **OdoBan®** can be used on nonporous surfaces such as walls, tables, floors, chairs, countertops, bathroom fixtures, sinks, shelves, racks and carts. **OdoBan®** may be used in hospitals, medical and dental offices, nursing homes, day care centers, nurseries, restaurants and bars, cafeterias, institutional facilities, public restrooms, institutions, schools, athletic facilities, camp grounds, play grounds, public facilities, transportation terminals, hotels and motels, factories, business and office buildings, buses, ambulances, trains and taxis.

Excellent for fire restoration.

HOW TO APPLY

Apply use-solution by thoroughly wetting surfaces as recommended and required with a cloth, mop, sponge or sprayer. For sprayer applications, adjust sprayer to coarse spray setting. Apply 6-8 inches from surface. Clean with a brush, sponge or cloth. Do not breathe spray.

DEODORIZER DIRECTIONS

Air Freshener: 22 oz. per gallon of water (1:5) or desired concentration will effectively neutralize damp musty odors caused by mildew in storage areas, basements, closets, bathrooms and A/C filters. Effective on smoking and cooking odors (garlic, fish, onions, etc.). Automobile odors from tobacco, musty carpet smell and beverage smells will be eliminated. **Laundry:** Add 8 oz. per load during the final rinse cycle to control laundry malodors, soften and eliminate static cling without damaging fibers. **Pet Odors:** 32 oz. per gallon of water (1:3) for urine, feces and vomit on carpet and upholstery. Clean prior to application then spray onto affected areas. Test hidden area for colorfastness. Allow 10 minutes contact time. Then blot with clean cloth. Allow to dry. Also effective on pet bedding and litter boxes. **Sewage Backup, Water Damage, Fire Restoration:** 16 oz. per gallon of water (1:7) or desired concentration to spray over affected areas before and after cleaning and extraction. Allow 10 minutes contact time. Use proper ventilation; open windows. **Carpets:** 8 oz. per gallon of water (1:15) eliminates odors associated with urine, vomit, smoke and mildew. Reapply after cleaning for freshening effects. Allow to dry. **Cleaning Solution:** 4 oz. per gallon of water (1:31) for cleaning kitchen counters, tables, walls, bathrooms, toilet seats, mopping floors and large routine applications. **RV Holding Tanks: Toilet waste:** Cover bottom of holding tank with water and add 6 oz. **Kitchen waste:** 2 oz. to gray water tank as needed to control malodors created by dirty dishwater.

DISINFECTION DIRECTIONS

OdoBan® is a Hospital Disinfectant for precleaned surfaces at 5 oz. per gallon of water. Bactericidal according to the AOAC Use Dilution Test Method, and a Mildewstat according to the EPA Mildew-Fungistatic guidelines against germs

‡such as *Pseudomonas aeruginosa*, *Salmonella choleraesuis*, *Staphylococcus aureus* (Staph), *Streptococcus pyogenes* (Strep), Methicillin Resistant *Staphylococcus aureus* (MRSA), Vancomycin Resistant *Enterococcus faecalis* (VREF), *Escherichia coli* (*E. coli*) 0157:H7, *Listeria monocytogenes*, *Serratia marcescens*, *Aspergillus niger*. **Disinfection Directions:** Remove heavy soil, then thoroughly clean surfaces. Apply use-solution to hard, nonporous surfaces as required. Treated surfaces must remain wet for 10 minutes. **Fungicidal Disinfection:** At 7 oz. per gallon, this product is an effective fungicide against *Trichophyton mentagrophytes*. Follow disinfection directions. **Mold & Mildew Control:** To control mold and mildew on hard, nonporous surfaces, wash visible soil from the surface. Then apply use solution, 5 oz. per gallon of water, with mop, sponge, cloth or trigger spray so as to wet all surfaces thoroughly. Let air dry. Repeat application every 7 days to control reoccurrence of growth.

VRUCIDAL* DIRECTIONS

OdoBan®, at 5 oz. per gallon of water, is Virucidal* according to the virucidal qualification against germs ‡such as: *Herpes Simplex Type 2, Influenza A/Hong Kong, HIV-1 (AIDS Virus). **Virucidal* Directions:** Follow disinfection directions. Treated surfaces must remain wet for 60 seconds. **KILLS HIV ON PRECLEANED ENVIRONMENTAL SURFACES/OBJECTS PREVIOUSLY SOILED WITH BLOOD/BODY FLUIDS**, in health care settings or other settings in which there is an expected likelihood of soiling of inanimate surfaces/objects with blood or body fluids and in which the surfaces/objects likely to be soiled with blood or body fluids can be associated with the potential for transmission of human immunodeficiency virus Type 1 (HIV-1) (associated with AIDS). **"SPECIAL INSTRUCTIONS FOR CLEANING AND DECONTAMINATION AGAINST HIV-1 ON SURFACES/OBJECTS SOILED WITH BLOOD/BODY FLUIDS"** **Personal Protection:** Clean-up should always be done wearing protective latex gloves, gowns, masks and eye protection. **Cleaning Procedure:** Blood and other body fluids containing HIV must be thoroughly cleaned from surfaces and objects before application of this product. **Contact Time:** Leave surface wet for 60 seconds. Use a 10 minute contact time for disinfection against all other bacteria and fungi claimed. **Disposal of Infectious Materials:** Blood, body fluids, cleaning materials and clothing should be autoclaved and disposed of according to local regulations for infectious waste disposal.

SANITIZER DIRECTIONS

OdoBan® is a sanitizer for precleaned, hard and nonporous nonfood contact surfaces according to the method for Inanimate Nonfood Contact Surface Sanitizer in 60 seconds at 5 oz. per gallon of water against germs †such as *Streptococcus pyogenes* (Strep), *Escherichia coli* 0157:H7 (*E. coli*) (pathogenic strain), *Listeria monocytogenes*, *Staphylococcus aureus* (Staph), *Klebsiella pneumoniae*. **Sanitizing:** Remove heavy soil, then thoroughly clean surfaces. To sanitize, apply use-solution to nonfood contact surfaces as required. Let stand 60 seconds then wipe.

PRECAUTIONARY STATEMENTS

Hazards to Humans and Domestic Animals. DANGER—Causes irreversible eye damage. Do not get in eyes or on clothing. Wear protective eyewear (goggles, face shield or safety glasses). Avoid contact with skin. Wash thoroughly with soap and water after handling. Remove contaminated clothing and wash clothing before reuse.

FIRST AID

If in Eyes: Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. **If on Skin or Clothing:** Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. **If Swallowed:** Call a poison control center or doctor immediately for

treatment advice. Have person sip a glass of water if able to swallow. Do not induce vomiting unless told to do so by a poison control center or doctor. Do not give anything by mouth to an unconscious person. **Note to Physician:** Probable mucosal damage may contraindicate the use of gastric lavage. Call a poison control center or doctor for treatment advice. Have the product container or label with you when calling a poison control center or doctor, or going for treatment.

STORAGE AND DISPOSAL

Store in areas inaccessible to small children. Do not reuse or refill this container. Offer for recycling, if available.