

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P400117-104

## Evoke

Mixed finishes, such as Polished Nickel with silver ridge accents are highlighted in new versions of the popular Evoke chandelier. This updated design features an oversized oval form with candelabra lights that complement a livable Luxe style, as well as Transitional and Mid-Century interiors.

- Mixed metal finishes highlight popular dual toned home décor accents
- Updated design features an oversized oval form with candelabra lights
- Polished Nickel with silver ridge accents
- Uses five 60-watt max. candelabra style bulbs including LED equivalent (sold separately)
- Complements a livable Luxe style, as well as Transitional and Mid-Century interiors.
- Ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or traditional living room settings
- Can be displayed individually or in groupings of two or more for customized design statements

**Category:** Chandeliers

**Finish:** Polished Nickel (plated)

**Construction:** Steel construction

**Glass/Shade:** Clear Glass Cylinder



**Diameter:** 33-3/4"  
**Height:** 27-7/8"  
**Overall Ht. W/Chain:** 103"

**Glass**  
**Width:** 3"  
**Height:** 9"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Hanging mounted</p> <p>Mounting strap for outlet box included</p> <p>Six feet of 9 gauge chain supplied</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>5.125" W., 0.875" ht., 5.125" depth</p>	<p>15 feet of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Five 60w max. candelabra</p> <p>E12 base</p>	<p>cULus Dry location listed</p> <p>1 year limited warranty</p>