

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4319-09

Replay

Replay features a linear form that provides a pleasingly elegant accent to your home. A sleek, metallic finish is complemented by white glass diffusers for a clean, modern silhouette.

- Smooth forms and linear details.
- Pleasingly elegant frame.
- Simplified modern look.
- Etched glass shade.
- Brushed Nickel finish
- Fixture can be installed with glass facing up or down.

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass/Shade: Etched glass shades



Diameter: 21"
Height: 19-5/8"
Overall Ht. W/Chain: 95"

Glass
Width: 5-1/8"
Height: 3-7/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied covers a standard 4" octagonal recessed outlet box	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 100w max. Medium Base E26 base socket	cULus Dry location listed